

RJ45 Slim Network Cable Cat.8.1 U/FTP angled up to 40 Gbps black 0.25 m

Description

This network cable by Delock can be used to connect various devices and is suitable for 40GBASE-T Ethernet applications with a frequency of 2 GHz and a data transfer rate of up to 40 Gbps.

With angled connectors

The connectors can be angled in any direction, e.g. to the right, left, up or down. They also allow space-saving installation in narrow places.

Slim patch cable

The thin patch cables are characterised by their small cable diameter and enable flexible and space-saving cabling in the network cabinet.



Item no. 80938

EAN: 4043619809387

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x RJ45 plug
1 x RJ45 plug
- Cat.8.1 specification
- Data transfer rate up to 40 Gbps
- Bandwidth: 2000 MHz
- Shielded (U/FTP)
- Slim
- Maximum angle: 60°
- Cable gauge: 32 AWG
- Connectors gold-plated: 50 u"
- Cable diameter: ca. 3.8 mm
- Cable jacket material: LSZH (halogen-free)
- Operating temperature: -20 °C ~ 60 °C
- Colour: black
- Length: ca. 0.25 m

Package content

- RJ45 cable

Images



General

Specification:	Cat. 8.1
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 male
Connector 2:	1 x RJ45 male

Technical characteristics

Operating temperature:	-20 °C ~ 60 °C
------------------------	----------------

Physical characteristics

Cable gauge:	32 AWG
Material:	LSZH (halogen-free)
Shielding:	U/FTP
Length:	0.25 m
Colour:	black
Cable diameter:	3.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de