

Impact Wrench

33851 / 33852

- Nickel chrome molybdenum square drive
- Variable speed trigger
- Muffled on handle exhaust

New Twin Hammer



1"
33851



1"
33852

33841 / 33842



1"
33841



1"
33842

KT NO.	Square drive Inch mm	Type Std/Long anvil	Std. bolt size Inch mm	Free speed R.P.M	Max. torque ft-lb N-m	Overall length Inch mm	Air inlet Inch	Air hose ID	Air pressure bar psi	Avg. air consumption L/min CFM	Sound DBA	Vib M/S2	Net weight kgs lbs	
33851-120	1"	25.40 Std. anvil	1-17/64" M32	5500	1200 1626	8-53/64" 224	3/8"BSPT	1/2"	6.2 90	269 9.5	99.75	6.57	5.64 12.43	1 / 4
33851-121	1"	25.40 Std. anvil	1-17/64" M32	5500	1200 1626	8-53/64" 224	3/8"NPT	1/2"	6.2 90	269 9.5	99.75	6.57	5.64 12.43	1 / 4
33852-120	1"	25.40 Long anvil	1-17/64" M32	5500	1200 1626	14-1/64" 356	3/8"BSPT	1/2"	6.2 90	269 9.5	98.00	8.40	6.04 13.32	1 / 4
33852-121	1"	25.40 Long anvil	1-17/64" M32	5500	1200 1626	14-1/64" 356	3/8"NPT	1/2"	6.2 90	269 9.5	98.00	8.40	6.04 13.32	1 / 4
33841-180	1"	25.40 Std. anvil	1-27/64" M36	4000	1800 2440	12-3/32" 307	1/2" BSPT / NPT	3/4"	6.2 90	255 9.0	101.56	4.37	10.62 23.41	1 / 2
33842-180	1"	25.40 Long anvil	1-27/64" M36	4000	1800 2440	20-5/64" 510	1/2" BSPT / NPT	3/4"	6.2 90	255 9.0	99.85	5.87	12.52 27.60	1 / 2