

Premium HDMI Cable 4K 60 Hz 5 m

Description

This certified premium HDMI cable by Delock can be used to connect devices with an HDMI interface, such as televisions, Blu-ray players, monitors or projectors. By supporting a maximum bandwidth of 18 Gbps, content can be displayed with resolutions of up to 4K Ultra HD (3840 x 2160 @ 60 Hz).

Perfect shielding guarantees loss-free signal transmission

The cable is characterised by the additional metal shielding of the plugs and the gold-plated contacts. It guarantees interference-free audio and video signal transmission thanks to its triple shielding and particularly dense braiding.



Item no. 84966

EAN: 4043619849666

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x HDMI-A male >
 - 1 x HDMI-A male
- Certified Premium HDMI cable
- High Speed HDMI with Ethernet (HEC) specification
- Cable gauge: 30 AWG
- Cable diameter: ca. 5.7 mm
- Twisted-pair cabling
- Copper conductor
- Triple shielded cable
- Contacts gold-plated
- Transmission of audio and video signals
- Data transfer rate up to 18 Gb/s
- Resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- 3D support: up to 1920 x 1080 @ 60 Hz; 3840 x 2160 @ 30 Hz
(depending on the system and the connected hardware)
- Supports the 21:9 cinema aspect ratio
- Supports 1080p HFR (High Frame Rate) 3D
- Up to 120 Hz refresh rate

- Supports transmission of 2 video channels simultaneously to use one display for two viewers
- Supports colour sampling in 4:2:0 format (original format of Blu-Ray, DVD and TV)
- Contains Audio Return Channel (ARC)
- Up to 32 audio channels for speakers
- Up to 1536 kHz audio sampling rate
- Supports transmission of up to 4 audio channels simultaneously
- Supports dynamic adjustment of lip synchronicity for audio / video delays
- Supports CEC 2.0 control commands
- Supports Dolby® TrueHD and DTS-HD Master Audio™
- Supports HDR
- More lively and natural colours
- Colour: black
- Length incl. connectors: ca. 5 m

System requirements

- A free HDMI-A interface



Package content

- Premium HDMI cable

Images



HDMI Cable with braiding and foil shielding



General

Specification:	HDMI 2.0
Style:	both sides identical

Interface

Connector 1:	1 x HDMI-A male
Connector 2:	1 x HDMI-A male

Technical characteristics

Data transfer rate:	up to 18 Gb/s
Maximum screen resolution:	3D: 3840 x 2160 @ 30 Hz 3840 x 2160 @ 60 Hz
Maximum refresh rate:	120 Hz

Physical characteristics

Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	30 AWG
Shielding:	triple
Length:	5 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de