


Fiber Optic Adapter Panel LC Duplex OM4 12 Port aqua

Description

This panel by Delock is equipped with twelve LC Duplex couplers and is suitable for installation in 19" fiber optic HD (High Density) patch panel by Delock (66924). With the LC Duplex couplers, fiber optic male connectors can be easily connected to each other.



Item no. 66933

EAN: 4043619669332

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 12 x LC Duplex female >
 - 12 x LC Duplex female
- For 24 OM4 Multi-mode fibers
- Zirconia ceramic ferrule with protection cap
- For mounting in 19" fiber optic HD (High Density) patch panel, 1U
- 12 ports with LC Duplex couplers
- Material: metal / plastic
- Colour: aqua / black
- Dimensions (LxWxH): ca. 109 x 35 x 20 mm


System requirements

- 19" fiber optic HD (High Density) patch panel

Package content

- Fiber optic adapter panel

Images



Interface

Connector 1:	12 x LC Duplex female
Connector 2:	12 x LC Duplex female

Physical characteristics

Material:	metal / plastic
Length:	109 mm
Width:	35 mm
Height:	20 mm
Colour:	aqua black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

