



## BETA 7246NB BASIC suede shoe, perforated



### Certifications and Standards



S1P FO SR

EN ISO 20345:2022

### Features

Perforated suede 7246NB shoe with elastic steel penetration proof insole and steel toe cap for cost-effective protection.

#### FIRST QUALITY PRICE

The perfect balance of durability, functionality and economy. Protection and reliability at your fingertips: safety at work has never been so accessible.

#### STEEL/STEEL PROTECTION

Maximum safety, low cost: our BASICS with steel toe cap and sheet provide reliable and durable protection for all pockets.

#### NEW STANDARD EN ISO 20345:2022

The shoe is S1P FO SR certified according to the latest EN ISO 20345:2022 standard. It is ideal for even the most demanding working environments, thanks to improved slip, oil and penetration resistance.



#### FUNCTIONAL DESIGN

The clean and essential lines are enhanced by bright orange details.



#### LUG OUTSOLE

The anti-static outsole with tread guarantees maximum slip and oil resistance.



#### PROTECTIVE GUSSET

Gusseted tongue protects the foot from annoying infiltration of liquids and debris.



## Certifications and Standards



## Specifications

LACING:	traditional
WEIGHT (INDICATIVE SIZE 42):	650 g
TYPE:	low

### Lightness

Perforated suede

### Comfort

Dual-density polyurethane

### Safety



Felt carbon

### Protections

Tip: Steel, 200 joules

Durability: Steel insole

## Coded items

	Art.	EU	UK	 mm
072461635	7246NB 35	35	2,5	228
072461636	7246NB 36	36	3,5	235
072461637	7246NB 37	37	4,5	242
072461638	7246NB 38	38	5	248
072461639	7246NB 39	39	6	255
072461640	7246NB 40	40	6,5	262
072461641	7246NB 41	41	7	268
072461642	7246NB 42	42	8	275
072461643	7246NB 43	43	9	282
072461644	7246NB 44	44	10	288
072461645	7246NB 45	45	10,5	295
072461646	7246NB 46	46	11	302
072461647	7246NB 47	47	12	308
072461648	7246NB 48	48	13	315

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

