

# Cable HDMI-A female > HDMI-A female panel-mount 4K 30 Hz 1 m

## Description

This cable by Delock can be used to extend an HDMI connection and to connect various devices. The female port can be attached with two screws, e.g. to a slot bracket, a cable duct or an enclosure with the corresponding opening. In this way, it is possible to install a HDMI connector in an easily accessible position.



**Item no. 85466**

EAN: 4043619854660

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:
  - 1 x HDMI-A 19 pin female >
  - 1 x HDMI-A 19 pin female panel-mount
- High Speed HDMI with Ethernet (HEC) specification
- Screw type: #4-40 UNC
- Mounting hole: ca. 15 x 6 mm, screw hole pitch ca. 30 mm
- Cable gauge: 28 AWG
- Cable diameter: ca. 7.3 mm
- Gold-plated connectors
- Transfer of audio and video signals
- Data transfer rate up to 10.2 Gb/s
- Resolution up to 3840 x 2160 @ 30 Hz  
(depending on the system and the connected hardware)
- 3D support up to 1080p in two video streams with each 60 pictures per second
- Supports Dolby® TrueHD and DTS-HD Master Audio™
- Colour: black
- Length incl. connectors: ca. 1.0 m

## System requirements

- A free HDMI interface

---

## Package content

- HDMI panel-mount cable
- 2 screws

---

## Images



## General

|                |                      |
|----------------|----------------------|
| Specification: | HDMI 1.4             |
| Style:         | both sides identical |

## Interface

|              |                   |
|--------------|-------------------|
| Connector 1: | 1 x HDMI-A female |
| Connector 2: | 1 x HDMI-A female |

## Technical characteristics

|                            |                     |
|----------------------------|---------------------|
| Data transfer rate:        | 10.2 Gbps           |
| Maximum screen resolution: | 3840 x 2160 @ 30 Hz |

## Physical characteristics

|                 |             |
|-----------------|-------------|
| Pin finishing:  | gold-plated |
| Cable gauge:    | 28 AWG      |
| Screw distance: | 30 mm       |
| Screw type:     | #4-40 UNC   |
| Length:         | 1 m         |
| Colour:         | black       |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |