






height
width
depth



General Information

1. ME 12,5 UT
 2. Foot catch
 3. Marking area
 4. PCB guidance
 5. Mounting rail like EN 60715:TH 35-7,5/15 or mounting rail TH 35-15x1,5 similar to EN 60715
- ⊕ Workpiece zero point for mechanical processing

- Simplified representation, exemplary shown in gray
- Document excluded from change process
- CAD Data see Download-Center on www.phoenixcontact.com
- Linear dimensions [mm]
- Tolerances apply in a normal climate according to DIN EN ISO 291-23/50-2, PA plastic parts with about 2% (% by weight) moisture content.
- Recommended PCB outline on www.phoenixcontact.com webcode: #0512

	DIN A3	document-No. / RI		date	scale
		00845839 / 02		19.12.2025	1:1
	ident.-No.	document-type			
	2869430	TECDOC 2D_Productdrawing			
	description		ME 12,5 UT KMGY		
page 1	of 1				