

RJ45 Network Cable Cat.6A plug to plug with robust latch and Cat.7 raw flat cable U/FTP 0.3 m black

Description

This network cable by Delock can be used to connect different networking devices, e.g. a NIC to a switch or a patch panel.

Super flexible and flat

The RJ45 cable is ideal for laying under carpets, floors or behind wallpaper. The material of the cable sheath is flexible and makes the cable very resistant to strain.

With robust latch

The robust RJ45 plug is ideal for industrial applications where plugs must be plugged and unplugged frequently. Compared to conventional plugs, the industrial plug can be plugged and unplugged up to 2,000 times without the latching lug will be bent or breaking off.



Item no. 80343

EAN: 4043619803439

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x RJ45 plug Cat.6A
 - 1 x RJ45 plug Cat.6A
- Cat.7 specification
- Bandwidth: 600 MHz
- Shielded (U/FTP)
- RJ45 plug with robust latch
- Up to 2,000 plug and bending cycles
- Connectors gold-plated: 50 µm
- Cable gauge: 32 AWG
- Cable size: ca. 6.0 x 1.9 mm
- Cable jacket material: PVC
- Colour: black
- Length: ca. 0.3 m

System requirements

- A free RJ45 jack

Package content

- RJ45 cable

Images



General

Specification:	Cat. 7
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 male
Connector 2:	1 x RJ45 male

Physical characteristics

Cable gauge:	32 AWG
Material:	PVC
Shielding:	U/FTP
Length:	0.3 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de