

	1	2	3	4	5	6	7	8	
F	5P	20~24	MSAP-05BFFC-SL700I		REV.	ECN NO.	DATE	SIGN	DESCRIPTION
	4P	20~24	MSAP-04BFFC-SL700I		E	C210977	2021/06/23	Vicky	△EXI
	Contacts	Applicable wire gauge	Item No.		F	C230009	2023/01/03	Vicky	△EXI
			△G		G	C241084	2024/09/25	Yunchen	△GX3
E	△C MSAP-XXBFFC-SL700I XX: No. Of Pin								
	△G								
D									
	PE Bag								
C									
	4P 5P								
B	Pin Assignments Front View								
A	UNIT:mm				TITLE		ITEM NO		
	TOLERANCE	△D			N SEN, M12 A -PLASTIC, SCREW CABLE W/O SR, F, F, FI/PANEL CRIMP		DRAWN BY		
	.X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°	△D			SCALE Free SIZE A4 SHEET 1 OF 1		Yunchen		
		REV. G WC-REV. .0			QC: Inspection item		DATE 2024/09/25		
				Amphenol LTW		DWG NO			CHECKED BY
				安費諾亮泰企業股份有限公司		MSAP-XXBFFC-SL700I			Aric
						CUSTOMER			APPROVED BY
						ALTW			Fred
									DATE 2024/09/25
									8 W10814-03-2001A2

△D
Note:
* RoHS Compliant
* Ⓞ Important Dimension
△F * Waterproof rate: IP67, mated
* Connector
Housing: Thermoplastic, Black
Pin: Copper alloy, Gold plated
Extension Nut: Thermoplastic, Black
Nut: Thermoplastic, Black
△C O-Ring: Rubber, Gray
* Clamp Ring: Thermoplastic, Black
* Sealing Nut: Thermoplastic, Black
△C * Seal: Rubber, Gray, OD:Ø4.0mm~Ø8.0mm
△E * Applicable wire gauge: 20AWG~24AWG
* One set unassembled in one pe bag

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.