UM-05

MONITOR SPRING DESK MOUNT 17” – 40”

SPRING MECHANISM

CABLE MANAGEMENT

75 × 75
100 × 100
VESA COMPATIBLE

ERGONOMIC SCREEN SETTING

UP TO 12 KG WEIGHT CAPACITY

17” - 40”
SCREEN SIZE





EN TECHNICAL SPECIFICATION

- Screen size compatibility: 17” - 40”
- Max weight capacity: Up to 12 kg for standard screen, up to 11 kg for curved screen
- VESA compatibility: 75 × 75, 100 × 100
- Tilt range: +80° ~ -45°
- Swivel range: +90° ~ -90°
- Screen rotation: +180° ~ -180°
- Arm full extension: 455 mm
- Material: Steel, aluminium, plastic
- Surface finish: Powder coating
- Dimensions of product: 120 × 508 × 587 mm
- Weight of product: 2.78 kg
- Color: Black
- Installation: Clamp, grommet
- Desktop thickness for clamp: 10 – 80 mm
- Desktop thickness for cable grommet: 10 – 40 mm
- Package contents: Monitor desk mount, mounting elements, user manual



The mechanism, based on a durable mechanical spring, allows for smooth and effortless adjustment of the monitor’s height and position. Thanks to this solution, you can adjust the screen’s position to your current needs at any time with just a single hand movement. Proper weight balancing of the display prevents it from dropping on its own and guarantees stability during everyday work and intense gameplay.

MODEL: UM-05

EAN: 5907264119941

Elmak Sp. z o.o.
al. Żołnierzy I Armii WP 20B
35-301 Rzeszów, Polska
www.savio.pl