

MS-D1ST-03

Monitor desk stand, full motion

- Stylish design with tempered glass base
- Position your screen perfectly for an optimal ergonomic position
- Compact space saving solution



Features

- Height adjustable monitor desk stand with tempered glass base
- Easy stepless height adjustment up to 420 mm
- Allows to swivel and tilt your display and enables rotating the display from landscape-to-portrait mode
- Works with almost any LCD monitor (max. 32" / 9 kg)
- Stable glass base plate for secure placement on any desk
- Built-in cable management for an organized and neat workspace
- VESA compatible, max. 100 x 100 mm

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

4
0.030017725
11.01
410x70x220 mm
433x235x295 mm
CN
8716309135252
8302500000

Package contents

Monitor stand
User manual

Specifications

Material: Steel, plastic, tempered glass
Surface finish: powder coating
Color: Matte black
Fit screen size: 17" 32"
Weight capacity: max. 9 kg
VESA compatible: 75 x 75, 100 x 100 mm
Height adjustment: max. 420 mm
Tilt range: +45° ~ -45°
Swivel range: +90° ~ -90°
Screen Rotation: +180° ~ -180°
Net weight: 2.5 kg
Dimensions: 390 x 280 x 454 mm

Certificates

