

# USB 2.0 Type-A built-in female with cable plug 30 cm aluminium

## Description

This cable by Delock can be used e.g. for installation in a panel or housing with a suitable opening. It can also be used to extend and connect various USB devices.



30 cm

**Item no. 88181**

EAN: 4043619881819

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:
  - 1 x USB 2.0 Type-A male
  - 1 x USB 2.0 Type-A female for installation
- Thread type: M22
- Built-in hole Ø: 23.7 mm
- Data transfer rate up to 480 Mbps
- Cable gauge:
  - 28 AWG data line
  - 24 AWG power line
- Cable diameter: ca. 4.5 mm
- Colour: black / silver
- Length incl. connectors: ca. 30 cm

## Package content

- USB cable

## Images



### Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type-A female for installation

### Physical characteristics

Cable gauge:	28 AWG data line 24 AWG power line
Length:	30 cm
Colour:	black silver
Cable diameter:	4.5 mm

### Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de