



Click [here](#) for the 3D model.

Dimensions	
D	25mm MAX
T	19mm MAX
LL	15mm +/-2mm
S	7mm
S1	17mm
Wire Size	1.1mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	300
Typical Component Weight	20 g

General Information	
Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	0.65 mH (100 kHz)
Current	7 A
Temperature Range	-40/+105°C
DC Resistance	14 mOhms