

Delock Cable DisplayPort 1.2 male > DisplayPort male 4K 1 m

Description

This cable enables the connection between devices with a DisplayPort interface, e.g. monitors or TVs, to a PC or a laptop. DisplayPort is a standardized universal connecting standard by VESA for the transfer of video and audio signal.



Item no. 83805

EAN: 4043619838059

Country of origin: China

Package: Zip poly bag

Technical details

- Connector:
DisplayPort 20 pin male >
DisplayPort 20 pin male
- DisplayPort 1.2 specification
- Pin 20 not connected
- Cable gauge: 28 AWG
- Cable diameter: ca. 7.3 mm
- Copper conductor
- Triple shielded cable
- Gold-plated connector
- Transfer of audio and video signals
- Data transfer rate up to 21.6 Gb/s
- Resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Colour: black
- Length incl. connector: ca. 1 m

System requirements

- A free DisplayPort interface

Package content

- DisplayPort cable

Images



General

Specification:	DisplayPort 1.2a
Style:	both sides identical

Interface

Connector 1:	1 x DisplayPort male
Connector 2:	1 x DisplayPort male

Technical characteristics

Data transfer rate:	21.6 Gbps
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Housing material:	PVC
Connector finishing:	nickel-plated
Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	28 AWG
Shielding:	triple
Length:	1 m
Colour:	black
Cable diameter:	7.3 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de