

USB 2.0 Bluetooth Adapter 4.0 dual mode

Description

The ultra-mini USB 2.0 Bluetooth adapter enables a wireless communication or data transfer e.g. between two PCs or a PC and a mobile phone. This Bluetooth adapter can remain plugged in the laptop since it stands out only 7 mm from the USB port. The adapter works as dual mode dongle and does not require high power due to the Bluetooth 4.0 standard. Furthermore it can easily be connected with end devices.

Bluetooth



Item no. 61889

EAN: 4043619618897

Country of origin: China

Package: Retail Box

Technical details

- Connectors: 1 x USB 2.0 Type-A male
- Chipset: Broadcom
- Bluetooth standard 4.0 dual mode + EDR
- Class 2, operating range up to 10 meter
- Frequency range: 2.4 - 2.4835 GHz ISM band
- Data transfer rate up to 3 Mbps
- USB bus powered
- Dimensions (LxWxH): ca. 19.5 x 16.0 x 8.1 mm

System requirements

- Windows 7/7-64/8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- USB 2.0 Bluetooth adapter
- Driver CD
- User manual

Images



Interface

Connector 1:	1 x USB 2.0 Type-A male
--------------	-------------------------

Technical characteristics

Data transfer rate:	up to 3 Mbps
Frequency range:	2.4000 GHz - 2.4835 GHz

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de