


RoHS Compliance

REV	Revision Record	Appr.	Date
V0	New Version Release	WuHao	2026-04-27
V1.0	Size Change	WuHao	2026-06-08
V2.0	Specifications Change	WuHao	2026-10-28







Material:
Molded Case:PA66+20%GF,UL 94 V-0,Yellow
Terminal:C3604,Gold Plated

Electrical Parameters:
Rated Voltage:DC 500V
Rated Current:30A
Contact Resistance:1.0mΩ
Insertion Force:18~45N
Pull Out Force:18~45N
LIfe:1000 Cycles
Operating Temperature:-40°C ~+125°C

Order Information:
L-KLS1-XT60-F-8

L: RoHS
Product series
Type:F-Female
Color:
8-Yellow

ANGLE TOLERANCE	PROJECTION		Description:	XT60 Connector,Female
±3°				
GENERAL TOLERANCE	UNITS	mm	KLS P/N:	L-KLS1-XT60-F-8
x.x ±0.30	SHEET SIZE	A4		
x.xx ±0.20	Draw:	WuHao	2026-04-27	NingBo KLS ELECTRONIC CO.,LTD.
x.xxx ±0.10	Check:	Daniel	2026-04-27	