

# Product Datasheet

Item No.: 60271

PRODUCT NAME

## Rubber extension for construction site 1-way 10 m H07RN-F 3G1,5 RD IP44



- Approved for use on construction sites and in agricultural applications
- IP44: protected against foreign bodies and splash-proof
- Approved for use on construction sites and in agricultural applications
- Shock-proof plug and shock-proof connector with protective cap
- 230 V, 16 A

Reference image

### Technical data

EAN	4011160602719
Weight [kg]	1.55
Dimensions	22x6x22 cm
Main color	red
Category	Extensions
Subcategory	For use on construction sites
Cable type	H07RN-F
Cross section [mm <sup>2</sup> ]	3G1,5
Cable color	red
Cable length [m]	10
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
IP protection	IP44
Input	Shock-proof plug 230 V, 16 A, IP44
Output	1x shock-proof connector with protective cap 230 V, 16 A, IP44
Total number of sockets	1
Number of Type F sockets (230 V)	1
Number of cores	3

Your partner for professional lighting and electrical products.