

Cable USB 2.0 Extension, active 30 m

Description

This USB 2.0 cable by Delock can be connected to an active USB port and enables an extension of 30 m. The higher cable gauge for power and data line ensures even at this length, a safe connection for your devices.



30 m

Item no. 83453

EAN: 4043619834532

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male >
 - 1 x USB 2.0 Type-A female
- Chipset: FE 1.1
- For connection to an active USB port
- Cable gauge:
 - 26 AWG data line
 - 22 AWG power line
- Contacts gold-plated
- Power: up to max. 500 mA
- Cable length: ca. 30 m


System requirements

- Linux Kernel 3.2 or above
- Mac OS 10.9 or above
- Windows Vista/Vista-64/7/7-64/8.1/8.1-64/10/10-64/11
- PC or laptop with a free active USB Type-A port

Package content

- USB 2.0 extension cable 30 m

Images



General

Specification:	USB 2.0
Supported operating system:	Linux Kernel 3.2 or above Mac OS 10.9 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows Vista 32-bit Windows Vista 64-bit Windows 11

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x USB 2.0 Type-A female

Technical characteristics

Chipset:	FE1.1
Data transfer rate:	480 Mbps
Maximum current:	500 mA

Physical characteristics

Pin finishing:	gold-plated
Cable gauge:	26 AWG data line 22 AWG power line
Length:	30 m

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland

E-Mail	info@delock.de
Website	www.delock.de