

MA-DA2-06

Desk mounted adjustable double monitor arm 17"-32", black

- Position your screen perfectly
- Lightweight and tilting design



Features

- Monitor desk mount with double monitor arms
- Arms rotate, extend and retract, tilt to change reading angles, and allow to rotate displays from landscape-to-portrait mode, etc
- Enables easy ergonomic positioning for reduced strain
- Works with almost any LCD monitor (max. 32")
- Durable adjustable gas-springs suitable for monitors of up to 10 kg
- Strong desk clamp for easy and secure fixation on your desk
- Detachable VESA plate enables easy installation

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

4
0.066825
18
425x270x115 mm
495x450x300 mm
CN
8716309135443
8302500000

Package contents

Desk arm
User manual
Mounting accessories

Specifications

Material: aluminum, steel
Surface finish: powder coating
Color: black
Fit screen size: 17" ~ 32"
Weight capacity: 2 ~ 10 kg (per display)
VESA compatible: 75 x 75, 100 x 100 mm
Tilt range: +90 ° ~ -45 °
Swivel range: +90 ° ~ -90 °
Screen Rotation: +180°~-180°
Installation: Desk clamp
Max. desk thickness clamp: 10 ~ 50 mm
Cable management: Yes

Certificates

