



| | | | |
|------------------------|---------------|---------------------------|------------|
| EAN: | 4013288018281 | Size: | 58x20x3 mm |
| Part number: | 05021015001 | Weight: | 3 g |
| Article number: | 950 | Country of origin: | CZ |

Customs tariff number: 82041100

- L-keys for hexagonal socket screws
- Wear-resistant size marking
- L-keys with Hex-Plus advantage for a longer screw life
- High corrosion protection thanks to chrome-plating
- Metric

High quality L-keys for hexagonal socket screws. Hex-Plus offers a larger contact surface within the screw head. This reduces the notching effects to a minimum and almost completely eliminates the risk of destroying the screw recess. The precise chrome-plated design ensures high corrosion protection.

Web link

https://products.wera.de/en/l-keys_l-keys_for_hexagon_socket_screws_950.html

Wera - 950

05021015001 - 4013288018281

L-Keys



We questioned the classic L-key design, since all too often the screw head recess is rounded out, meaning screws can no longer be tightened or loosened - and so the user finds the L-key slipping out of the recess. Wera Hex-Plus tools have a larger contact surface in the screw head. The notching effects are reduced and thereby the deformation of the screws. At the same time, as much as 20 % more torque can be applied.

Hex-Plus



Hexagon screws can endure a problem because the contact surfaces delivering the power from the conventional tool, is transferred to the screw via very small surface areas. The consequence: the screw can become damaged (rounding out). Hex-Plus tools have a greater contact surface that prevents this from happening! At the same time, as much as 20 % more torque can be applied. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

Size identification



The size of each L-keys has been engraved by a laser. In addition Take it easy L-keys have a colour coding according to sizes - for simple and rapid accessing of the required tool. Making it easy to find the right tool.

Surface protection



Chrome-plated hexagon L-keys for outstanding surface protection and long service life. High corrosion protection.

Web link

https://products.wera.de/en/l-keys_l-keys_for_hexagon_socket_screws_950.html

Wera - 950

05021015001 - 4013288018281

Further versions in this product family:

| |  | mm | mm | mm | inch | inch |
|---------------------------|---|-----------|-----------|---------------|--------------|---------|
| 05021005001 ¹⁾ | | 1.5 | 45 | 14 | 1 3/4 | 9/16 |
| 05021010001 | | 2.0 | 50 | 16 | 2 | 5/8 |
| 05021015001 | 2.5 | 56 | 18 | 2 7/32 | 23/32 | |
| 05021020001 | | 3.0 | 63 | 20 | 2 1/2 | 25/32 |
| 05021025001 | | 3.5 | 66 | 23 | 2 5/8 | 29/32 |
| 05021030001 | | 4.0 | 70 | 25 | 2 3/4 | 1 |
| 05021035001 | | 4.5 | 75 | 26 | 3 | 1 1/32 |
| 05021040001 | | 5.0 | 80 | 28 | 3 1/8 | 1 3/32 |
| 05021045001 | | 6.0 | 90 | 32 | 3 1/2 | 1 1/4 |
| 05021050001 | | 7.0 | 95 | 34 | 3 3/4 | 1 5/16 |
| 05021055001 | | 8.0 | 100 | 36 | 4 | 1 7/16 |
| 05021060001 | | 9.0 | 106 | 38 | 4 3/16 | 1 1/2 |
| 05021065001 | | 10.0 | 112 | 40 | 4 7/16 | 1 9/16 |
| 05021070001 | | 11.0 | 120 | 43 | 4 3/4 | 1 11/16 |
| 05021075001 | | 12.0 | 125 | 45 | 5 | 1 3/4 |
| 05021080001 | | 13.0 | 132 | 50 | 5 3/16 | 2 |
| 05021085001 ¹⁾ | | 14.0 | 140 | 56 | 5 1/2 | 2 7/32 |
| 05021090001 ¹⁾ | | 17.0 | 160 | 63 | 6 5/16 | 2 1/2 |
| 05021095001 ¹⁾ | | 19.0 | 180 | 70 | 7 1/16 | 2 3/4 |
| 05021100001 ¹⁾ | | 22.0 | 200 | 80 | 8 | 3 1/8 |
| 05021105001 ¹⁾ | | 24.0 | 224 | 90 | 9 | 3 1/2 |
| 05021110001 ¹⁾ | | 27.0 | 250 | 100 | 10 | 4 |

1) Regular hexagon.

Web linkhttps://products.wera.de/en/l-keys_l-keys_for_hexagon_socket_screws_950.html

Wera - 950

05021015001 - 4013288018281

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de