

UTP Cat6 Patch cord, grey, 1 m, copper

PP6U-CU-1M

- Perfect connection
- Gold plated contacts



Specifications

Category: category 6
 Type: UTP (unshielded)
 Frequency bandwidth: Max. 250 MHz
 Compliance with ANSI / TIA / EIA-568B standards
 Conductor: AWG 26 4P(7 x 0.16 mm wire), pure copper
 Conductor insulation: HDPE 0.85 mm
 Shielding: n/a
 LDPE filler: yes
 Polyester tape: n/a
 Drain wire: n/a
 Jacket material: PVC
 Jacket braiding: n/a
 Jacket outer diameter: 6.2 mm
 Length: conform item description
 Color: conform item description

Features

- Copper CAT6 stranded unshielded (UTP) patch cord, 8P8C
- Snagless boots

Packaging

Q'ty in crtn, pcs	200
Crtn volume, CUM	0.036
Crtn weight, kgs	7.04
Individual package size LxWxH:	130x180x15 mm
Carton size LxWxH:	400x300x300 mm
Country of origin	CN
Barcode	8716309131292
Customs code	8544421000

Certificates

