

Adapter DisplayPort 1.1 female > DisplayPort female panel-mount

Description

This adapter by Delock can be used to extend a DisplayPort connection and to connect various devices. The female port can be attached with two screws, e.g. to a slot bracket, a cable duct or an enclosure with the corresponding opening. In this way, it is possible to install a DisplayPort connector in an easily accessible position.



Item no. 85123

EAN: 4043619851232

Country of origin: China

Package: Zip poly bag

Technical details

- Connector:
 - 1 x DisplayPort 20 pin female with screw nuts for installation >
 - 1 x DisplayPort 20 pin female
- Screw type: #4-40 UNC
- Mounting hole ca. 18 x 7 mm, screw hole pitch ca. 27 mm
- DisplayPort 1.1 specification
- Pin 20 is connected (supports 3.3 V)
- Supports a resolution up to 1920 x 1080 @ 60 Hz (depending on the system and the connected hardware)
- Gold-plated connector
- Colour: black
- Dimensions (LxWxH): ca. 42,2 x 35,3 x 13,3 mm

System requirements

- A free DisplayPort port

Package content

- DisplayPort adapter panel-mount
- 2 screws

General

Specification:	DisplayPort 1.1
Style:	both sides identical

Interface

Connector 1:	1 x DisplayPort 20 pin female panel-mount
Connector 2:	1 x DisplayPort female

Technical characteristics

Maximum screen resolution:	1920 x 1080 @ 60 Hz
----------------------------	---------------------

Physical characteristics

Length:	42.2 mm
Width:	35.3 mm
Height:	13.3 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de