




4.6 / 4.8

Selon choix du
fournisseur

BN 354

Vis de poêliers

à fente

Acier 4.6 / 4.8

zingué-bleu

[3D Cadenas](#)

Article#	d ₁	d ₂ max.	k max.	n min.	t~	L
3056144	M4	10	3	1,1	1,3	6
1486594						8
1486608						10
1486616						12
1486624						16
1486632						20
3056145	M5	12	4	1,3	1,5	8
1136798						10
1233467						12
1136801						16
1136828						20
1136836						25
1136844						30
1136852						35
1136860						40
3056147	M6	14	4,2	1,6	2	8
1136879						10
1233548						12
1136887						16
1136895						20
1136909						25
1136917						30
1136925						35
1136933						40
1136941						45
3056149						50

Article#	d ₁	d ₂ max.	k max.	n min.	t~	L
3056150	M8	17	4,4	1,8	2,7	16
1136968						20
1136976						25
1136984						30
1136992						35
1137018						40
1137026						45
1137034						50
3056155						60