





P/N LEGEND

A2004	WV	-2XNP	N	X	X	XX	N	XX	G
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩
① Series No.									
② Connector type: WV=Vertical									
③ No. of circuits									
④ N=Halogen Free									
⑤ Material: 0=Nylon 66+15%GF,UL94V-0 L=LCP-V0 6=Nylon 6T									
⑥ Color: W=White B=Black N=Natural									
⑦ Plating code for contacts: T1=Tin-plated G1=Gold-flash G5=Gold-plated 15u"									
⑧ Plating code: N=Non-plating									
⑨ Option code: 00=Dim.F=3.00 Y6=Dim.F=2.25									
⑩ Packing code: G=Bag									

SPECIFICATIONS

Current Rating: 3A AC,DC
Voltage Rating: 250V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 10mΩ Max.
Insulation Resistance: 1000MΩ Min.
Withstanding Voltage: 800V AC/minute
Pin Material: Brass

Circuit No.	Dimensions				Circuit No.	Dimensions			
	A	B	C	D		A	B	C	D
2X02P	2.00	6.00	4.70	---	2X14P	26.00	30.00	28.70	24.00
2X03P	4.00	8.00	6.70	2.00	2X15P	28.00	32.00	30.70	26.00
2X04P	6.00	10.00	8.70	4.00	2X16P	30.00	34.00	32.70	28.00
2X05P	8.00	12.00	10.70	6.00	2X17P	32.00	36.00	34.70	30.00
2X06P	10.00	14.00	12.70	8.00	2X18P	34.00	38.00	36.70	32.00
2X07P	12.00	16.00	14.70	10.00	2X19P	36.00	40.00	38.70	34.00
2X08P	14.00	18.00	16.70	12.00	2X20P	38.00	42.00	40.70	36.00
2X09P	16.00	20.00	18.70	14.00	2X21P	40.00	44.00	42.70	38.00
2X10P	18.00	22.00	20.70	16.00	2X22P	42.00	46.00	44.70	40.00
2X11P	20.00	24.00	22.70	18.00	2X23P	44.00	48.00	46.70	42.00
2X12P	22.00	26.00	24.70	20.00	2X24P	46.00	50.00	48.70	44.00
2X13P	24.00	28.00	26.70	22.00					

					燦達電子工業股份有限公司		
B3	EN202508062039	2025.08.06	吳清		JOINT TECH ELECTRONIC IND. CO., LTD.		
B2	EN202310251473	2023.10.19	吳清		UNIT	SCALE	SHEET
B1	EN202211171226	2022.11.18	張澤繪		mm	1 : 1	1 of 1
B0	EN202210111193	2022.10.11	徐貴湖	DRAWN BY		APPROVED BY	
A5	EN202204211028	2022.04.21	徐貴湖	陳錦展		董正一	
A4	EN1612060002	2016.12.06	賴永強	2011.05.12		2011.05.12	
A3	EN1607060001	2016.07.06	劉建芳	GENERAL TOLERANCE			
A2	EN1304070101	2013.03.11	唐騰鳳				
A1	EN1112050511	2011.12.05	陳錦展	X. X±0. 25	ANGLE±		
A0	NEW RELEASE	2011.05.12	陳錦展	X. XX±0. 15			
REV.	DESCRIPTION	DATE	NAME	X. XXX±0. 05			
				DRAW NO. : A2004WV-2XNPNXXXXXXG			
				REV. B3			