

CAT5e UTP Patch cord, pink, 2 m

PP12-2M/RO

- Perfect connection
- For a reliable connection
- Gold plated contacts



Features

- Unshielded patch cord, 8P8C
- 50u" gold plated contacts
- Molded strain reliefs

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

100
0.025
5.2
190x165x60 mm
300x400x210 mm
CN
8716309077873
8544421000

Specifications

Patch cord Enhanced category 5 UTP (unshielded)
Length: according to the item
Structure: AWG 26 (7 0.15 mm wire), CCA
HDPE insulation of the wire: 0.81 mm
With LDPE filler: not used
With polyester tape: not used
With aluminum foil: not used
Drain hose: not used
Braid: not used
PVC outer insulation: 5.0 mm
Color: according to the item
Operation up to 100 MHz

Certificates

