

USB 2.0 OTG Cable Type Micro-B male to Type-A female 11 cm

Description

This cable by Delock allows the connection between USB devices, such as memory sticks or external hard drives, and mobile devices equipped with a Micro USB port. The OTG function enables a direct data transfer between the mobile device and the USB device, without the connection to a computer.



OTG / 11 cm

Item no. 83018

EAN: 4043619830183

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 Type Micro-B male
 - 1 x USB 2.0 Type-A female
- OTG function (On-The-Go)
- Cable gauge:
 - 28 AWG data line
 - 24 AWG power line
- Cable diameter: ca. 4.7 mm
- Data transfer rate up to 480 Mbps
- Colour: black
- Length incl. connectors: ca. 11 cm

System requirements

- Mobile device with OTG support and Micro USB port

Package content

- USB 2.0 cable

Images



General

Specification:	OTG (On-The-Go) USB 2.0
----------------	----------------------------

Interface

Connector 1:	1 x USB 2.0 Type Micro-B male
Connector 2:	1 x USB 2.0 Type-A female

Technical characteristics

Data transfer rate:	480 Mbps
---------------------	----------

Physical characteristics

Cable gauge:	28 AWG data line 24 AWG power line
Length:	11 cm
Colour:	black
Cable diameter:	4.7 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de