

Adapter Thunderbolt™ 3 male > 2 x DisplayPort female 4K 60 Hz

Description

This Delock adapter is suitable for the connection of two DisplayPort monitors to a computer with Thunderbolt™ 3 interface. Due to Thunderbolt™ 3 technology, the adapter supports a resolution up to 4K Ultra HD at 60 Hz on both monitors.



Item no. 62708

EAN: 4043619627080

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x Thunderbolt™ 3 USB Type-C™ 24 pin male
 - 2 x DisplayPort female
- Chipset: Intel DSL6540
- Thunderbolt™ 3 and DisplayPort 1.2 specification
- Data transfer rate up to 40 Gbps
- Maximum resolution:
 - 1 display: up to 5120 x 2880 @ 60 Hz
 - 2 displays: up to 4096 x 2160 @ 60 Hz
 - (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Functions: Mirrored or Extended
- Thunderbolt™ 3 bus powered
- Plug & Play
- Dimensions of the adapter (LxWxH): ca. 99 x 60 x 16 mm
- Cable length without connectors: ca. 27 cm
- Colour: black

System requirements

- Mac OS 10.12 or above

- Windows 7/7-64/8.1/8.1-64/10/10-64/11
- PC or laptop with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

Package content

- Adapter Thunderbolt™ 3 to 2 x DisplayPort

Images



General

Function:	Plug & Play
Specification:	DisplayPort 1.2 Thunderbolt™ 3
Supported operating system:	Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

Output:	2 x DisplayPort female
Input:	1 x Thunderbolt™ 3 USB Type-C™ 24 pin male

Technical characteristics

Data transfer rate:	Thunderbolt™ 3 up to 40 Gb/s
Maximum screen resolution:	4096 x 2160 @ 60 Hz

Physical characteristics

Cable length:	27 cm
Length:	99 mm
Width:	60 mm
Height:	16 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de