

## KS 18 LTX 57 (601857840) Cordless Circular Saw

18V ; MetaLoc

Order no. 601857840

EAN 4007430327345



Product may differ from image



- Powerful, light, cordless circular saw for universal use on construction sites
- Aluminium base plate can be directly used on guide rails from Metabo and other manufacturers
- Fast brake stops the saw blade quickly and improves safety
- Accurately angled bevel cuts down to 50°, with handy snap-in point at 45°
- 0° position re-adjustable for highest cutting precision
- Clearly visible cutting indicator for precise sawing after initial cut
- Handle with non-slip soft-grip surface for safe guidance
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Battery packs with capacity display for checking the charge status
- Ultra-M technology: highest performance, gentle charging and 3 years of warranty on the battery pack.

**Technical data****Characteristics**

Battery voltage	18 V
Swivel range from / to:	0 / + 50 °
Adjustable cutting depth	0 - 57 mm // 0 - 2 1/4 "
Maximum cutting depth at 90°	57 mm / 2 1/4 "
Maximum cutting depth at 45°	43 mm / 1 11/16 "
Saw blade Ø x bore	165 x 20 mm / 6 1/2 x 5/8 "
No-load speed	4600 rpm
Max. cutting speed	40 m/s / 129 ft/min
Weight (including battery pack)	3.4 kg / 7.5 lbs

**Vibration**

Sawing chipboards	2.5 m/s <sup>2</sup>
Uncertainty of measurement K	1.5 m/s <sup>2</sup>

**Noise emission**

Sound pressure level	92 dB(A)
Sound power level (LwA)	103 dB(A)
Uncertainty of measurement K	3 dB(A)

**Scope of delivery**

Carbide circular saw blade (18 teeth)

MetaLoc case

without battery pack, without charger

Parallel guide / rip fence

Hexagonal wrench

Hexagonal wrench