

	ISO 14583			4.8
---	-----------	--	--	-----

**BN 30503****Viti a testa cilindrica bombata**

con cava esalobata, interamente filettate

Acciaio 4.8

zincato bianco



A causa della geometria della testa è necessario utilizzare coppie di serraggio ridotte.

Article#	d ₁	d ₂ max.	k max.		t max.	A~	L
5401271	M3	5,6	2,4	X10	1,27	2,8	5
5001994							6
5002109							8
5401272							10
5401273							12
3212090							16
5401274	M4	8	3,1	X20	1,66	3,95	6
5002079							8
5401279							10
5002060							12
5401280							16
3278487							20
5401275	M5	9,5	3,7	X25	1,91	4,5	8
5401276							10
5401277							12
3221340							14
5401278							16
5401281							20
3221372							25
5401282	M6	12	4,6	X30	2,42	5,6	10
5401283							12
5401284							16
5401285							20
5401286							25