

Coiled Cable EASY-USB 2.0 Type-A male to USB Type-C™ male 0.5 m to 0.8 m black

Description

This coiled cable by Delock with EASY-USB Type-A male can be plugged into the appropriated USB female port in both directions. Thus the male connector can be used both-sided which makes the plug in easier.

Coiled Cable

The coiled cable enables a flexible connection, is easy to store and unlike conventional cables, takes up less space. It also has a high restoring force and can be extended to three times its original length.



Item no. 90133

EAN: 4043619901333

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A reversible male
 - 1 x USB 2.0 Type-C™ male
- USB-A male port usable in both directions
- Data transfer rate up to 480 Mb/s
- Flexible
- Coiled length:
 - min.: 150 mm
 - max.: 450 mm
- Expansion ratio: 3:1
- Cable gauge:
 - 28 AWG data line
 - 24 AWG power line
- Cable diameter: ca. 4.0 mm
- Contacts gold-plated
- Cable jacket material: TPU
- Output current: 2 A
- Colour: black
- Length pulled together incl. connectors: ca. 0.5 m
- Length extended incl. connectors: ca. 0.8 m

Package content

- USB coiled cable

Images



Interface

Connector 1:	1 x USB 2.0 Type-A reversible male
Connector 2:	1 x USB 2.0 Type-C™ male

Physical characteristics

Cable gauge:	28 AWG data line 24 AWG power line
Length:	0.8 m
Colour:	black
Cable diameter:	4 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de