

USB Type-C™ Adapter to HDMI 4K 30 Hz with USB Type-A and USB Type-C™ PD

Description

This adapter by Delock is suitable for the connection of a **HDMI monitor** to a computer with **USB-C™** interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface.



USB Power Delivery (USB PD 2.0) support up to 60 watt

The adapter has a USB Type-C™ Power Delivery port to connect the power supply of the laptop or tablet to charge it.

Item no. 64091

EAN: 4043619640911

Country of origin: China

Package: Retail Box

Please Note

When used on a smartphone, an additional power supply may be required if the monitor output and a USB memory device are connected at the same time.

Technical details

- Connectors:
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ male >
 - 1 x HDMI-A 19 pin female
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) Type-A female - Battery Charging specification BC1.2
 - 1 x USB Type-C™ Power Delivery female (optional for power supply)
- Chipset: Algotek AG6310
- DisplayPort 1.2 and High Speed HDMI with Ethernet (HEC) specification
- Resolution up to 3840 x 2160 @ 30 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Input power: 1 x USB Type-C™ female max. 60 W
- Supports 3D displays
- Supports HDCP 1.4
- USB bus powered
- Plug & Play
- Cable length without connectors: ca. 15 cm
- Colour: black

System requirements

- Android 8.0 or above
- Chrome OS 75.0 or above
- Mac OS 10.14.6 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to HDMI Adapter + USB Type-A

Images



General

Function:	Plug & Play
Specification:	HDCP 1.4 HDMI 2.0
Supported operating system:	Android 8.0 or above Chrome OS 75.0 or above Mac OS 10.14.6 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit

Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	1 x HDMI-A female
Connector 3:	1 x USB Type-C™ Power Delivery female
Connector 4:	1 x USB 5 Gbps Type-A female - Battery Charging specification BC1.2

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 30 Hz
Signal transmission:	video audio

Physical characteristics

Housing material:	Plastic
Cable length:	15 cm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland

E-Mail	info@delock.de
Website	www.delock.de