

# Adapter DisplayPort 1.1 male to DVI female Passive black

## Description

This adapter by Delock enables the connection of an **DVI monitor** to the system via a free DisplayPort interface.



15 cm

**Item no. 61008**

EAN: 4043619610082

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x DisplayPort male
  - 1 x DVI 24+5 female with nuts
- Chipset: NXP PTN3361
- DVI-D (Single Link), VGA not wired
- DisplayPort 1.1 specification
- Passive converter (level shifter), suitable only for graphics cards with DP++ output
- Resolution up to 1920 x 1200 @ 60 Hz (depending on the system and the connected hardware)
- Standby detection, standby enter into sleep mode automatically
- 1 x ferrite core
- Cable length without connectors: ca. 15 cm
- Colour: black
- OS independent, no driver installation necessary

## System requirements

- A free DisplayPort DP++ female port

## Package content

- Adapter DisplayPort to DVI

---

## Images



### Interface

Connector 1:	1 x DisplayPort male
Connector 2:	1 x DVI 24+5 female with nuts

### Technical characteristics

Chipset:	NXP PTN3361
Maximum screen resolution:	1920 x 1200 @ 60 Hz

### Physical characteristics

Ferrite core:	1 x
Cable length:	15 cm
Colour:	black

### Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de