



# SHOBO SH8F

## PC CASE

### PRODUCT FEATURES:

- Four efficient Fury Sai S12 PWM fans with FDB bearings ensure high operating culture and optimal air circulation.
- The refreshed front panel with modern styling provides an attractive look and high airflow for improved cooling.
- The design allows for the installation of AIO radiators in 240/280/360 mm sizes at the front and 240 mm on top of the case.
- The spacious interior allows for the installation of graphics cards up to 330 mm in length and CPU coolers up to 161 mm in height.
- A modern I/O panel with USB 3.0 ports and space for three SSD/HDD drives guarantee extensive system expansion possibilities.

### PRODUCT SPECIFICATION:

Type of casing	Midi Tower
Motherboard form factor	ATX, Micro-ATX, Mini-ITX
The maximum length of the PSU	170 mm
Maximum CPU cooling height	161 mm
Maximum length of the GPU graphics card	330 mm
I/O panel	Mini Jack x2, USB 3.0 Typ-A x2, USB 2.0 Typ-A x1
Installed fans	4x 120 mm
Max number of fans	8
Support for installation of fans - top	2x 120 mm, 1x 140 mm
Support for installation of fans - front	3x 120 mm, 3x 140 mm
Support for installation of fans - rear	1x 120 mm
Support for installation of liquid cooling - top	120 mm, 240 mm
Support for installation of liquid cooling - front	120 mm, 140 mm, 280 mm, 360 mm
Support for installation of liquid cooling - rear	120 mm
Number of 2.5" drive bays (SSD/HDD)	2
Number of 3.5" drive bays (SSD/HDD)	2
Material	ABS, Steel, Tempered Glass
Dimensions	336 x 200 x 437 mm
Weight	4,3 kg

