



BETA 7202BP

Leather shoe, smooth-finished,
water repellent



Certifications and Standards



S3S FO SR

EN ISO 20345:2022

Features

The 7202B metal-free water-repellent smooth leather footwear guarantees maximum durability and versatility with

FIRST PRICE METAL FREE

The 7202BP provides protection without metal parts, offering greater comfort and versatility of use, at a competitive price

WIDE FOOTBED

The wide fit further enhances the comfort of the shoe, preventing possible constriction of the foot at any time of day.

NEW STANDARD EN ISO 20345:2022+A1:2024

The shoe is S3 S FO SR certified according to the latest EN ISO 20345:2022+A1:2024 standard. It is ideal for even the most demanding working environments, thanks to improved slip, oil and penetration resistance.



TRADITIONAL LACING

With traditional lacing, the laces can be adjusted for a secure and customised fit, ensuring perfect comfort with every step.



PROTECTIVE GUSSET

Gusseted tongue protects the foot from annoying infiltration of liquids, dust and debris.



Certifications and Standards

CE

S3S FO SR

EN ISO 20345:2022



Specifications

LACING:	traditional
WEIGHT (INDICATIVE SIZE 42):	635 g
TYPE:	low

Lightness

Smooth-finished, water-repellent leather

Comfort

Dual-density polyurethane

Safety



Polyurethane foam

Protections

Tip: Polymer material, 200 joules

Durability: Composite fibre, ceramic treatment

Coded items

	Art.	EU	UK	 mm
072020635	7202BP 35	35	2,5	229
072020636	7202BP 36	36	3,5	236
072020637	7202BP 37	37	4,5	243
072020638	7202BP 38	38	5	250
072020639	7202BP 39	39	6	257
072020640	7202BP 40	40	6,5	264
072020641	7202BP 41	41	7	271
072020642	7202BP 42	42	8	278
072020643	7202BP 43	43	9	285
072020644	7202BP 44	44	10	292
072020645	7202BP 45	45	10,5	299
072020646	7202BP 46	46	11	306
072020647	7202BP 47	47	12	313
072020648	7202BP 48	48	13	320

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

