



FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人



PART NUMBER: LAS1-AJ-D/ Δ / \blacktriangle / \ast

" Δ "	CAP OR LAMP COLOR	" \blacktriangle "	LAMP VOLTAGE	" \ast "	PROTECTION DEGREE
R	RED	6V	AC/DC 6V	NO LETTER	IP40
G	GREEN	12V	AC/DC 12V	P	IP65
Y	YELLOW	24V	AC/DC 24V		
B	BLUE	110V	AC/DC 110V		
W	WHITE	220V	AC/DC 220V		

OTHER VOLTAGE CAN BE MADE TO ORDER

SPECIFICATIONS:

- 1.RATED CURRENT: 6V ABOUT 15mA; 12V ABOUT 12mA; 24V ABOUT 5mA; 110~220V ABOUT 2mA.
- 2.LAMP CIRCUIT: USING AC/DC LED LAMP,THE TERMINALS NO DIFFERENCE OF ANODE AND CATHODE.
- 3.LAMP LIFE: ABOUT 40,000 hours(REFERENCE).
- 4.INSULATION RESISTANCE: $\geq 1000M\Omega(500VDC)$.
- 5.DROPPING WAY: INNER RESISTANCE.
- 6.POWER-FREQUENCY WITHSTAND VOLTAGE: 1,500V, RMS 50Hz, 1min.
- 7.OPERATING TEMPERATURE: $-25^{\circ}C \sim +55^{\circ}C$ (NO FREEZING, KEEP THE AIR FLOWING AROUND PUSHBUTTON).
- 8.TORQUE: 0.6Nm Max. APPLIED TO NUT.
- 9.FRONT PANEL PROTECTION DEGREE: IP40/IP65.
- 10.TERMINAL TYPE: PIN TERMINAL(2.8X0.5mm).
- 11.GENERAL TOLERANCE: 0-18mm= ± 0.25 , 18-80mm= ± 0.52 .
- 12.RoHS CAN BE CUSTOMIZED.

- MATERIALS:
- 1.LAMP CAP: PC.
 - 2.BODY: PC.
 - 3.BASE: PBT.

BRAND 品牌		红波按钮制造有限公司		
ONPOW 欧宝龙®		ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.		
TITLE 名称	LAS1-A SERIES INDICATOR	\oplus \triangle	UNIT 单位	mm
DWG NO. 图号	LAS1-AJ-D	SCALE 比例	1.5 : 1	SIZE 图纸
FILE NAME 档案名称	LAS1-A信号灯 .DWG	DRAWN 制图	HCP 2024/05/04	SHEET 张
			1/1	REV. 版本
				V1.0