


19" Splice Box Front Panel 24 port LC Quad limegreen

Description

This front panel by Delock can be mounted in a 19" splice box by Delock.



Item no. 43374

EAN: 4043619433742

Country of origin: China

Package: White Box

Technical details

- Connectors:
 - 24 x LC Quad female >
 - 24 x LC Quad female
- Colour: limegreen
- For 96 OM5 Multi-mode fibers
- Zirconia ceramic ferrule with protection cap
- For mounting in 19" splice box, 1U
- Housing colour: black
- Dimensions (LxWxH): ca. 439.0 x 39.4 x 19.5 mm


System requirements

- Delock 19" Fiber Optic Splice Box 43350

Package content

- 19" splice box front panel
- 6 x screw

Images



General

Style:	both sides identical
--------	----------------------

Physical characteristics

Housing colour:	black
Depth:	19.5 mm
Width:	439.0 mm
Height:	39.4 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

