


Product Datasheet

Item No.: 860680

as
Schwabe
TechnikProdukte

PRODUCT NAME

Plug stake socket outlet 2xIP44 socket, H07RN-F 3G1,5 2 m "F"



- Weather-resistant, shatterproof special plastic
- With shock-proof socket outlets, splash-proof
- 2 m heavy-duty rubber cable H07RN-F 3G1,5
- IP44: protected against foreign bodies and splash-proof
- 230 V, 16 A

Reference image

Technical data

EAN	4059948001040
Weight [kg]	0.6
Dimensions	11x7x40 cm
Main color	black
Category	House and garden
Subcategory	Multi socket outlets & multiplugs
Cable type	H07RN-F
Cross section [mm ²]	3G1,5
Cable color	black
Cable length [m]	2
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
IP protection	IP44
Input	Shock-proof plug 230 V, 16 A, IP44
Output	2x shock-proof socket outlet 230 V, 16 A, IP44 "F"
Total number of sockets	2
Number of Type E sockets (230 V)	2

Your partner for professional lighting and electrical products.