

# USB Type-C™ Adapter to VGA (DP Alt Mode) - Key Chain

## Description

This adapter by Delock is suitable for the connection of a VGA monitor to a computer with USB-C™ interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface. Due to the small dimensions, the adapter is ideal as on the go companion.



**Item no. 63941**

EAN: 4043619639410

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:  
1 x USB Type-C™ male >  
1 x VGA 15 pin female
- Chipset: Realtek RTD2169U
- Resolution up to 1920 x 1080 @ 60 Hz  
(depending on the system and the connected hardware)
- USB bus powered
- Plug & Play
- Cable length without connectors: ca. 3 cm
- Colour: black

## System requirements

- Android 6.0 or above
- Chrome OS
- iPad Pro (2018)
- Linux Kernel 4.3.3 or above
- Mac OS 10.13.3 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64
- Windows 10 Mobile
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or

- PC or laptop with a free Thunderbolt™ 3 port

---

## Package content

- USB-C™ to VGA adapter

---

## Images



## General

|                             |                                                                                                                                                                                                                                                                   |
|-----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Function:                   | Plug & Play                                                                                                                                                                                                                                                       |
| Supported operating system: | Android 6.0 or above<br>Chrome OS<br>Linux Kernel 4.3.3 or above<br>Mac OS 10.13.3 or above<br>Windows 10 32-Bit<br>Windows 10 64-Bit<br>Windows 10 Mobile<br>Windows 7 32-Bit<br>Windows 7 64-Bit<br>Windows 8.1 32-Bit<br>Windows 8.1 64-Bit<br>iPad Pro (2018) |

## Interface

|         |                       |
|---------|-----------------------|
| Output: | 1 x VGA 15 pin female |
| Input:  | 1 x USB Type-C™ male  |

## Technical characteristics

|                            |                               |
|----------------------------|-------------------------------|
| Chipset:                   | Realtek RTD2169U<br>VIA VL100 |
| Maximum screen resolution: | 1920 x 1080 @ 60 Hz           |
| Signal transmission:       | video                         |

## Physical characteristics

|         |       |
|---------|-------|
| Colour: | black |
|---------|-------|

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |