

Adapter USB Type-C™ male > mini DisplayPort female (DP Alt Mode) 4K 60 Hz with PD function

Description

This Delock adapter is suitable for the connection of a DisplayPort monitor to a computer with USB-C™ interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like Macbook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface. The adapter has a USB Type-C™ Power Delivery port. This allows the laptop to be charged while the adapter is in use.

[Delock Monitor Adapter \(Video\)](#)



Item no. 62990

EAN: 4043619629909

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - Input:
 - 1 x USB Type-C™ male
 - 1 x USB Type-C™ Power Delivery female (optional for power supply)
 - Output:
 - 1 x mini DisplayPort 20 pin female
- Chipset: VIA VL100
- Resolution up to 4096 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Transfer of audio and video signals
- Charging power: max. 60 W, 20 V @ 3 A
- USB bus powered
- Plug & Play
- Housing material: aluminium
- 1 x ferrite core
- Cable length without connectors: ca. 20 cm
- Colour: dark grey

System requirements

- Windows 7/7-64/8.1/8.1-64/10/10-64, Windows 10 Mobile, Chrome OS, iPad Pro (2018),


Linux ex Kernel 4.3, Mac ex OS 10.12

- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ to mini DisplayPort adapter

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Linux Kernel 4.3 or above Mac OS 10.12 or above Windows 10 32-Bit Windows 10 64-Bit Windows 10 Mobile Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (2018)

Interface

Output:	1 x mini DisplayPort 20 pin female
Input:	1 x USB Type-C™ female (power supply) 1 x USB Type-C™ male

Technical characteristics

Chipset:	VIA VL100
Maximum screen resolution:	4096 x 2160 @ 60 Hz
Signal transmission:	video audio

Physical characteristics

Ferrite core:	1 x
Housing material:	Aluminium
Cable length:	20 cm
Connector finishing:	nickel-plated
Colour:	dark grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de