D-Type Module USB 2.0 Type-A female to female

Description

This module by Delock can be mounted e.g. in panels or cases with D-type openings for XLR jacks.
This makes it ideal for integrating digital equipment into professional audio systems.



Item no. 86784

EAN: 4043619867844

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
  external: 1 x USB 2.0 Type-A female >
  internal: 1 x USB 2.0 Type-A female
- Material: zinc die cast
- Colour: black
- For D-type ports with 24 x 19 mm
- Panel cut-out (diameter): ca. 24 mm
- Two mounting holes for screw fastening
- Dimensions (LxWxH): ca. 32.6 x 25.5 x 30.8 mm

Package content

- D-Type module

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Images



All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

General

Mounting type:	D-Type
Style:	both sides identical

Interface

External:	1 x USB 2.0 Type-A female
Internal:	1 x USB 2.0 Type-A female

Physical characteristics

Housing material:	zinc die cast
Length:	32.6 mm
Width:	25.5 mm
Height:	30.8 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**