Converter SCART / HDMI to HDMI with Scaler

Description

The Delock A/V converter converts an analogue SCART video and audio signal to a digital HDMI signal. Thereby e.g. a VCR or game console can be connected to an HDMI monitor or Full HD TV. In addition, an HDMI input is present, so that the converter can be used as a switch. Both inputs can be scaled via the integrated video processor to an HDMI output signal of 720p or 1080p with 50 or 60 Hz. The audio signal is simultaneously available at the HDMI output, as a digital S/PDIF signal and as analogue signal at the stereo jack.



Item no. 62783

EAN: 4043619627837

Country of origin: China

Package: Box

Technical details

- Connectors:
  Input:
  1 x SCART female (RGB or Composite)
  1 x HDMI-A 19 pin female
  1 x DC 5 V power connector
  Output:
  1 x HDMI-A 19 pin female
  1 x 3.5 mm 3 pin stereo jack female
  1 x Coaxial female S/PDIF
- Input switchable between SCART / HDMI
- Output switchable between 720p / 1080p, PAL / NTSC
- Resolution (SCART input) PAL / NTSC-M / NTSC 4.43 / SECAM / PAL-M / PAL-N
- Resolution (HDMI output) 1280 x 720 or 1920 x 1080 @ 50 or 60 Hz
- Supports stereo audio
- Dimensions (LxWxH): ca. 102 x 101 x 25 mm

Power supply specification

- Wall power supply
- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.3 A
- Output: 5 V / 1 A
- Ground outside, plus inside
- Dimensions:

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

inside: ø ca. 2.1 mm
outside: ø ca. 5.5 mm
length: ca. 9.5 mm

System requirements

- Monitor or TV with HDMI connector
- Connection cables

Package content

- Converter SCART / HDMI > HDMI
- External power supply
- User manual

Images





All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Allgemein

Spezifikation:	HDMI 1.3

Schnittstelle

Ausgang:	1 x 3,5 mm 3 Pin Klinkenbuchse 1 x Koaxial Buchse S/PDIF 1 x HDMI-A Buchse
Eingang:	1 x 5 V DC Buchse 5,5 mm x 2,1 mm 1 x SCART Buchse 1 x HDMI-A Buchse

Technische Eigenschaften

Maximale Bildauflösung:	1920 x 1080 @ 60 Hz

Physikalische Eigenschaften

Gehäusefarbe:	schwarz
Gehäusematerial:	Metall
Länge:	102 mm
Breite:	101 mm
Höhe:	25 mm

Netzteil

Netzteil Typ:	Euro-Steckernetzteil
Eingangsspannung:	AC 100 - 240 V / 50 - 60 Hz / 0,2 A
Netzteilausgang:	5,0 V / 1,0 A
Netzteilanschluss:	DC Stecker 5,5 mm x 2,1 mm
Kabellänge des Netzteils:	1 m

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**