

Adapter USB Type-C™ to 1 x Serial RS-232 DB9 with 15 kV ESD protection

Description

This USB Type-C™ to serial adapter by Delock provides an RS-232 port for meters, POS systems, printers, modems, IoT devices, etc. The three LEDs at the RS-232 port indicate the transmission and reception status as well as the USB power.



Item no. 64038

EAN: 4043619640386

Country of origin: Taiwan,
Republic of China

Package: White Box

Technical details

- Connectors:
1 x USB Type-C™ male
1 x serial RS-232 DB9 male
- Serial connector with nuts
- Chipset: FTDI FT231XS
- Data transfer rate up to 460.8 Kbps
- FIFO: 512 Byte - RX
- FIFO: 512 Byte - TX
- Databits: 7, 8
- Stop bits: 1, 2
- Parity: even, odd, none, mark, space
- Signals: TxD, RxD, RTS, CTS, DTR, DSR, DCD, RI, GND
- LED colour: red, orange, green
- ±15 kV ESD protection for all serial signals
- Operating temperature: -40 °C ~ 85 °C
- Cable length without connectors: ca. 15 cm

System requirements

- Linux Kernel 4.9 or above

- Mac OS 10.15 or above
- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-C™ or Thunderbolt™ 3 port

Package content

- USB Type-C™ to 1 x serial adapter
- Driver CD
- User manual

Images



General

Function:	Plug & Play
Specification:	RS-232 (EIA / TIA) USB Type-C™
Supported operating system:	Linux Kernel 2.6 or above Mac OS 10.13 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows 11
LED indicator:	PWR / RXD / TXD
Protection:	ESD (Electrostatic Discharge)

Interface

Output:	1 x Serial RS-232 DB9 male
Input:	1 x USB Type-C™ male

Technical characteristics

Operating voltage:	5 V / 90 mA
Chipset:	FTDI FT231XS
Data transfer rate:	460.8 Kbps
FIFO:	512 Byte
Signal transmission:	TxD, RxD, RTS, CTS, DTR, DSR, DCD, RI, GND
Data transmission:	asynchronous full duplex Bidirectional
UART:	USB to serial UART
Data bits:	7, 8

Physical characteristics

Housing material:	Plastic (ABS)
Weight:	26 g
Cable type:	UL Recognized Component UL AWM 2725 80 °C 30V
Cable colour:	black
Cable length incl. connectors:	25 cm
Pin finishing:	gold-plated
Cable gauge:	28 AWG data line 26 AWG power line
Shielding:	double
Colour:	black
Surge Protection:	15 kV
Thread type:	#4-40 UNC
Insulator:	PVC
LED colour:	red green orange
Cable diameter:	4.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de