

# Fiber Optical Cable with metal armouring LC Duplex to SC Duplex Multi-mode OM4 3 m

## Description

This fiber optical cable by Delock can be used to connect different networking devices, e.g. a switch to a media converter.

### With metal armouring

The robust fiber optical cables offer increased protection against damage and outer influences such as moisture, dust or damaging rodents. Despite the metal sheath, the cables remain bendable and flexible. The fiber optical cables are also characterised by their high tensile strength.



3 m

**Item no. 87918**

EAN: 4043619879182

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:  
1 x LC Duplex >  
1 x SC Duplex
- Multi-mode OM4 cable with metal armour
- Fibre: 50/125 µm
- Ceramic ferrule with dust protection
- Cable diameter: ca. 3 mm
- Operating temperature: -20 °C ~ 70 °C
- LSZH (halogen-free)
- Colour: violet
- Length incl. connectors: ca. 3 m

## Package content

- Optical fiber cable

## Images



## Interface

|              |               |
|--------------|---------------|
| Connector 1: | 1 x LC Duplex |
| Connector 2: | 1 x SC Duplex |

## Technical characteristics

|                        |                |
|------------------------|----------------|
| Operating temperature: | -20 °C ~ 70 °C |
|------------------------|----------------|

## Physical characteristics

|                 |                     |
|-----------------|---------------------|
| Material:       | LSZH (halogen-free) |
| Length:         | 3 m                 |
| Colour:         | violet              |
| Cable diameter: | 3 mm                |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |

