









General Information:

- Simplified representation, exemplary shown in gray.
- Document excluded from change process
- Units are in millimeters [mm] and degrees [°]
- Tolerances apply in a normal climate according to DIN EN ISO 291-23/50-2, PA plastic parts with about 2% (% by weight) moisture content.
-  Workpiece zero point for mechanical processing
- Tolerances for mechanical processing are ISO 2768-mK
- Tolerances for printing DIN ISO 2768-m
- In case of distortion there is no functional impact of the single part in the application.
- Web: www.phoenixcontact.com webcode: #1635

Additional Information:

- D. PCB position (t=1,5)
- E. Guidance between Cover and Housing
- F. Latching point between Cover and Housing
- C. Bottom side
- D. Marking area

Pos.	QTY	Description	Material		
1	1	L-COVER	PA		
 DIN A3		document-No. / RI 01367542 / 01		date 29.04.2025	scale 1:1
		ident.-No. 1224121		document-type TECDOC 2D_Productdrawing	
		description ME-IO 18,8 LC 10U 2RJ45 7035			
		page 1		of 1	