

USB 2.0 Cable 2 x USB Type-A male to 2 x USB Type-A female with screws for built-in 1 m black

Description

This cable by Delock can be used to extend and connect various USB devices. The built-in jack can be attached for e.g. to a dashboard in a car or to a housing with a suitable cut-out. In this way, it is possible to install a USB port in an easily accessible position.



Item no. 88105

EAN: 4043619881055

Country of origin: China

Package: Zip poly bag

Special features

- With inner metal thread

Technical details

- Connectors:
 - 2 x USB 2.0 Type-A male
 - 2 x USB 2.0 Type-A female with screws for built-in
- Data transfer rate up to 480 Mb/s
- Screw type: #4-40 UNC
- Pitch of screw hole: ca. 32 mm
- Cable gauge:
 - 28 AWG data line
 - 24 AWG power line
- Cable diameter: ca. 4.5 mm
- Cable jacket material: PVC
- Colour: black
- Length: ca. 1 m

System requirements

- Two free USB ports

Package content

- Cable

Images



Interface

Connector 1:	2 x USB 2.0 Type-A male
Connector 2:	2 x USB 2.0 Type-A female with screws for built-in

Technical characteristics

Data transfer rate:	480 Mbps
---------------------	----------

Physical characteristics

Cable gauge:	28 - 24 AWG
Material:	PVC
Length:	1 m
Colour:	black
Cable diameter:	4.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de