







Rating	30A 12V DC	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-20°C~85°C		
Switch Function	3P SPST ON-OFF (LED dependent)		



1 HEX NUT ASSY
1 SPRING WASHER ASSY
1 KNURL NUT ASSY



KEYWAY on "OFF"

Tolerances ± 0.3 Unless Otherwise Specified

08/04/'22	曾敏捷	依ECR(RAD20220729-359),將側面負極端子改到底部,并修改鐫雕內容			△4
12/02/'13	柳新強	依公司規定追加SCI Logo			△3
09/24/'07	C.J.Chan	Change Circuit Diagram			△2
04/18/'07	C.J.Chan	Updated rating 20A to 30A			△1
Date	Name	Description			NO
Drawn	Checked	Approved	SCI BOM NO.	1811845	Model Name TOGGLE SWITCH
曾敏捷			Customer No.		Model No. R13-404AL2-01-HWR
08/04/'22	8/4-'22	8/4-'22	Unit	mm	Shin Chin Industrial Co., Ltd.
					Rev. 4