

Adapter cable USB 2.0 Type-C™ male > USB 2.0 Type-A female 15 cm black

Description

This Adapter by Delock can be used for the connection of a USB device with USB Type-C™ interface and a standard USB Type-A port.



15 cm

Item no. 65579

EAN: 4043619655793

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB Type-C™ 2.0 male >
 - 1 x USB 2.0 Type-A female
- Cable gauge:
 - 30 AWG data line
 - 24 AWG power line
- Host = USB Type-C™; Device = USB Type-A
- Resistor: 5.1 kΩ
- Output current: up to 3 A
- Cable diameter: ca. 3 mm
- Data transfer rate up to 480 Mbps
- Colour: black
- Length incl. connectors: ca. 15 cm

System requirements

- PC or laptop with a free USB Type-C™ port or
- Smartphone or tablet with a free USB Type-C™ port

Package content

- USB-C™ adapter

Interface

Connector 1:	1 x USB 2.0 Type-C male
Connector 2:	1 x USB 2.0 Type-A female

Technical characteristics

Data transfer rate:	480 Mbps
Resistor:	5.1 kΩ

Physical characteristics

Cable gauge:	30 AWG data line 24 AWG power line
Colour:	black
Cable diameter:	3 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de