

1392
Młotki bezdrutowe

	art.	Ø mm	L mm	L1 mm	g
013920030	1392 30	30	300	105	575
013920035	1392 35	35	305	115	670
013920040	1392 40	40	310	125	796
013920050	1392 50	50	325	135	1206
013920060	1392 60	60	385	155	1505

