




WIRE LIST

- 1.CABLE:UL2725,USB CABLE,28AWG(7/0.12mm±0.008mm)×1PAIRS
+24AWG(7/0.2mm±0.008)×2C,TIN COPPER
INSULATOR:P.P FOR 28AWG&PVC FOR 24AWG
SHIELD:7/0.1mm+AL-FOIL+BRAID
JACKET:PVC,Ø.D:4.8mm±0.2mm,COLOR:BLACK COLOR
- 2.CONNECTOR:1 PCS USB A SOLDER TYPE MALE
- 3.HOOD:MOULDED TYPE,COLOR:BLACK COLOR
- 4.TUBE
- 5.ELECTRONIC TEST:100% OPEN,SHORT+MISS WIRE TEST
- 6.Fulfill ROHS Guideline

P1		OPEN END	
USB A MALE	WIRE COLOR		AWG
1	RED		24AWG
2	WHITE		1 PAIRS (28AWG)
3	GREEN		
4	BLACK		24AWG
SHELL	DRAIN WIRE+BRAID		

PART NO	CAB-USB-A-2.0-BK	SHEET NO	1	 THIRD ANGLE PROJECTION		NEWMAN HOPE&CO. INC. TEL:886-2-28765517 FAX:886-2-28765527 E-MAIL: sales@newmanhope.com.tw				
TITLE:USB A MALE TO OPEN END,L:2M,UL2725 BLACK COLOR				SCALE	N.T.S			DRAWN BY & DATE		
				SIZE	A4			CHECKED BY & DATE		
				UNIT						
DWN NO	D-CAB-USB-A-2.0-BK			☒ mm	☐ INCH	APPROVED BY & DATE				