

# USB Type-C™ Network Adapter 2.5 Gigabit LAN 1 x RJ45 ASIX

## Description

The adapter by Delock expands a PC or laptop by **one network interface** via the **USB Type-C™** interface.

### NBASE-T for higher speed

Modern services and new technologies require **higher bandwidths**. NBASE-T technology enables speeds of 1 Gbps and **2.5 Gbps** with conventional networking cables. The best possible transmission rate is set automatically.



**Item no. 66046**

EAN: 4043619660469

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB 5 Gbps USB Type-C™ male
  - 1 x 2.5 Gigabit LAN RJ45 jack
- Chipset: ASIX AX88279
- SuperSpeed USB - 5 Gbps specification
- Data transfer rate:
  - Ethernet up to 10 Mbps (Half/Full Duplex)
  - Fast Ethernet up to 100 Mbps (Half/Full Duplex)
  - Gigabit Ethernet up to 1000 Mbps (Half/Full Duplex)
  - NBASE-T with up to 2.5 Gbps (Half/Full Duplex)
- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- Support full duplex operation with IEEE 802.3x flow control and half duplex operation with back-pressure
- Supports 9k Jumbo Frames
- Supports MAC Address Passthrough
- LED indicator for link and activity
- USB bus powered
- Colour: black
- Cable length without connectors: ca. 15 cm
- Dimensions (LxWxH): ca. 75 x 35 x 15 mm

---

## System requirements

- Android 11.0 or above
- Chrome OS 113.0 or above
- Linux Kernel 3.10 or above
- Mac OS 10.6 or above
- Windows 10/10-64/11
- PC or laptop with a free USB Type-C™ or Thunderbolt™ 3 port


---

## Package content

- USB Type-C™ 2.5 Gigabit LAN adapter
- User manual

---

## Images



## General

Specification:	USB 5 Gbps
Supported operating system:	Chrome OS Linux Kernel 3.10 or above Mac OS 10.6 or above Windows 10 32-Bit Windows 10 64-Bit Windows 11 Android 11.0 or above
LED indicator:	Link and activity

## Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	1 x 2.5 Gigabit LAN RJ45 jack

## Technical characteristics

Chipset:	ASIX AX88279
Data transfer rate:	Ethernet up to 10 Mbps Fast Ethernet up to 100 Mbps Gigabit Ethernet up to 1000 Mbps Gigabit Ethernet up to 2.5 Gbps

## Physical characteristics

Cable length:	15 cm
Length:	75 mm
Width:	35 mm
Height:	15 mm
Colour:	black

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin

Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de